

Rittal – The System.

Faster – better – everywhere.



AS 4054.870 Cross member cutter

State: 28/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.870 - Cross member cutter

For cutting through micro webs or sheet steel cross members on Ri4Power interior installation components (for example, compartment dividers) or for cutting thin sheets of sheet steel, aluminium or copper up to 1.2 mm thick.



Features

Model No.	AS 4054.870
Design	Straight
Product description	For cutting through micro webs or sheet steel cross members on Ri4Power interior installation components (for example, compartment dividers) or for cutting thin sheets of sheet steel, aluminium or copper up to 1.2 mm thick.
Benefits	Cutting of materials without deformation Clean edge cuts, no reworking of the cut section required Easy to use Ergonomically styled handles for fatigue-free, non-slip working
Material	Tool body: Special tool steel, rolled, oil-hardened
Colour	Handle: Anthracite and Rittal Power Pink
Supply includes	Cross member cutter including swarf deflector

Features

To fit Model No.	9683.006 9683.008 9683.016 9683.018 9683.036 9683.038 9680.005 9680.025 9680.207 9680.227 9683.406 9683.408 9683.426 9683.428 9683.444 9683.446 9683.448 9683.464 9683.466 9683.468 9683.484 9683.486 9683.488
Dimensions	Length: 280 mm
Machinable material	Sheet steel Aluminium Copper Plastic
Maximum machinable material thickness, sheet steel	1.2 mm
Maximum machinable material thickness, aluminium	1.2 mm
Maximum machinable material thickness, plastic	2 mm
Cut width	2.7 mm
Packs of	1 pc(s).
Net weight	0.5

Features

Gross weight	0.54
Customs tariff number	82032000
EAN	4028177955929
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890