

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.080**

**Manual hydraulic punch set, M16 -  
M40**

State: 10/02/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.080 - Manual hydraulic punch set, M16 - M40

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

## Features

Model No.	AS 4055.080
Design	With 90° angled and 360° rotating cylinder head
Product description	Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in overpressure valve Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel
Supply includes	Manual hydraulic punch 5 splitter hole punches, triple splitting Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 10 mm Spacer sleeve set (3-part) Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm
Ø punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm

# Features

---

For threads	M16
	M20
	M25
	M32
	M40

---

Packs of	1 pc(s).
----------	----------

---

Net weight	4.1
------------	-----

---

Gross weight	4.16
--------------	------

---

Customs tariff number	84678900
-----------------------	----------

---

EAN	4028177807952
-----	---------------

---

ETIM 9	EC002121
--------	----------

---

ETIM 8	EC002121
--------	----------

---

ECLASS 8.0	21049046
------------	----------

---