

Rittal – The System.

Faster – better – everywhere.



AS 4055.080

**Manual hydraulic punch set, M16 -
M40**

State: 15/08/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.080 - Manual hydraulic punch set, M16 - M40

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

Features

Model No.	AS 4055.080
Design	With 90° angled and 360° rotating cylinder head
Product description	Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in overpressure valve Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel
Supply includes	Manual hydraulic punch 5 splitter hole punches, triple splitting Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 10 mm Spacer sleeve set (3-part) Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm
Ø punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm

Features

For threads	M16
	M20
	M25
	M32
	M40
Packs of	1 pc(s).
Net weight	4.1
Gross weight	4.16
Customs tariff number	84678900
EAN	4028177807952
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046