

Rittal – The System.

Faster – better – everywhere.



PS 4179.000

U nut

State: 25/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4179.000 - U nut

For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets.



Features

| | |
|-----------------------|---|
| Model No. | PS 4179.000 |
| Installation options | Punched rail 23 x 23 mm Punched section without mounting flange, 23 x 73 mm Punched section without mounting flange, 45 x 88 mm Punched section with mounting flange, 23 x 73 mm |
| Note | For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets, we recommend U nuts with M6 thread |
| Dimensions | Thread: M6 |
| Thread | M6 |
| Packs of | 20 pc(s). |
| Net weight | 0.34 |
| Gross weight | 0.378 |
| Customs tariff number | 73181692 |
| EAN | 4028177093300 |
| ETIM 9 | EC000096 |
| ETIM 8 | EC000096 |
| ECLASS 8.0 | 23110804 |