



TS 4697.000

Support strip

State: 07/05/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4697.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Model No.	TS 4697.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm pitch pattern
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	740 mm
VX installation options	In enclosure width/depth 800 mm
VX SE installation options	In enclosure width/depth 800 mm
AX installation options	In door width 800 mm, with cam lock
AX stainless steel installation options	In door width 800 mm, with cam lock, in conjunction with the perforated door strip
PC installation options	In enclosure width 800 mm, on the outer mounting level
TS installation options	In enclosure width/depth 800 mm, on the outer mounting level
AE installation options	In enclosure width/height 800 mm, in conjunction with rail for interior installation AE

Features

VX base/plinth installation options	In base/plinth width/depth 800 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket
To fit	Enclosure type: VX TS VX SE PC AX AE Width/depth: 800 mm
To fit	Base/plinth system VX
Packs of	20 pc(s).
Net weight	7.7 kg
Gross weight	7.817 kg
PCF per pack (cradle-to-gate)	29.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	TS Support strip, for VX, TS, VX SE, TP, for outer mounting level: for W/W, D: 800 mm, L: 740 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------