


# Rittal – The System.

Faster – better – everywhere.



## CM 5001.217 Gland plate

State: 09/09/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CM 5001.217 - Gland plate for TP

Potential equalisation is provided via assembly components and earthing points.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | CM 5001.217  |
| Product description   | Potential equalisation is provided via assembly components and earthing points.  |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Supply includes       | Assembly parts   |
| Note                  | For greater stability and universal cable entry, the base opening is divided in the width for 1000, 1200 and 1600 mm wide enclosures, and is suitable for various configurations.<br>Several gland module plates need to be combined to close off the base completely in the TS-IT |
| Dimensions            | Depth: 100 mm  |
| To fit                | Enclosure type: TS IT<br>TS<br>CM<br>TP<br>Width: = 1,200 mm   |
| Packs of              | 1 pc(s).   |
| Net weight            | 0.939  |
| Gross weight          | 0.94   |
| Customs tariff number | 94039910   |
| EAN                   | 4028177523210  |
| E-Number Sweden       | E3404485   |
| ETIM 9                | EC002620   |
| ETIM 8                | EC002620   |
| ECLASS 8.0            | 27189261   |