

Rittal – The System.

Faster – better – everywhere.



CM 5001.224 Gland plate

State: 10/07/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CM 5001.224 - Gland plate for TP

Potential equalisation is provided via assembly components and earthing points.

Features

| | |
|-----------------------|--|
| Model No. | CM 5001.224 |
| Product description | Potential equalisation is provided via assembly components and earthing points. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Note | For greater stability and universal cable entry, the base opening is divided in the width for 1000, 1200 and 1600 mm wide enclosures, and is suitable for various configurations. Several gland module plates need to be combined to close off the base completely in the TS-IT |
| Dimensions | Depth: 250 mm |
| To fit | Enclosure type: TS IT TS CM TP Width: = 1,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.5 |
| Gross weight | 1.521 |
| Customs tariff number | 73269098 |
| EAN | 4028177523289 |
| E-Number Sweden | E3404476 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |