

Rittal – The System.

Faster – better – everywhere.



VX 5302.103

482.6 mm (19") mounting angles, standard

State: 28/08/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.103 - 482.6 mm (19") mounting angles, standard for VX IT

Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design directly accommodates all commercially available installation kits for server installation kits for server systems, which are fastened directly to the 19" system punchings.

Features

| | |
|--------------------------|--|
| Model No. | VX 5302.103 |
| Design | for VX IT 482.6 mm (19") mounting angles, standard |
| Product description | Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design directly accommodates all commercially available installation kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings. |
| Benefits | Integral, bidirectional U labelling Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling |
| Technical specifications | Side punchings, round and square, on a U pitch pattern Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components 482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E |
| Applications | For mounting a 482.6 mm (19") mounting level within the VX IT rack system |
| Material | Sheet steel, 2 mm |
| Surface finish | Primed |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Mounting position | rear |

Features

| | |
|-------------------------------|--|
| Installation options | Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected |
| Assembly instruction | To be combined with cross-member, depth stays or mounting bracket for attachment Use of the different mounting options depends on the relevant enclosure dimensions |
| To fit | Height: = 24 U |
| Packs of | 2 pc(s). |
| Net weight | 5 |
| Gross weight | 5.24 |
| PCF per pack (cradle-to-gate) | 19.9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177955417 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |