
### Rittal - The System.

Faster – better – everywhere.





### DK 5302.202


# Cable management panel with brush strip

State: 14/12/2025 (Source: rittal.com/gr-en)



## DK 5302.202 - Cable management panel with brush strip 482.6 mm (19")

With cut-out 390 x 40 mm (2 U) or 390 x 20 mm (1 U) with brush insert, accommodation facility for cable clamp straps.



#### **Features**

| Model No.           | DK 5302.202  |
|---------------------|--|
| Product description | For convenient, simple cable routing between two areas separated<br>by a 482.6 mm (19") mounting level, for example, between the front<br>and rear areas of the 482.6 mm (19") mounting level. |
| Benefits            | To make the cable entry larger, two panels are easily combined with one another  |
| Applications        | For locking and simultaneous cable routing in installation zones to the 1 U, 482.6 mm (19") mounting standard  |
| Material            | Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free Brush strip fibres: Plastic PA6, halogen-free Brush strip mounting body: Plastic PVC, contains halogen                                |
| Surface finish      | Spray-finished   |
| Colour              | RAL 9005   |
| Mounting cut-out    | Width:390 mm<br>Height:30 mm   |
| Dimensions          | Width: 482.6 mm  |
| Units               | 1 U  |
|                     |  |

© Rittal 2025

### **Features**

| Packs of                      | 1 pc(s).   |
|-------------------------------|--|
| Net weight                    | 0.2  |
| Gross weight                  | 0.243  |
| PCF per pack (cradle-to-gate) | 0.9 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177952874  |
| ETIM 9                        | EC000322   |
| ECLASS 8.0                    | 27400604   |

© Rittal 2025 3