

Rittal – The System.

Faster – better – everywhere.



PC 5366.100

PC enclosure system

State: 17/09/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5366.100 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

Features

Model No.	PC 5366.100
Design	with glazed door at the top, folding keyboard and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.
Material	Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Viewing window: Single-pane safety glass
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated
Colour	Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: Similar to RAL 9006 Monitor panel, door centre part: RAL 7015
Supply includes	Enclosure, door, rear door Glazed door, top Folding keyboard Component shelf
Dimensions	Width: 600 mm Height: 1,600 mm Depth: 636 mm
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12

Features

Max. keyboard dimensions (WxHxD)	497 x 50 x 250 mm 497 x 60 x 200 mm
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	96
Gross weight	98
EAN	4028177693203
ECLASS 8.0	27180501

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Enclosure system with monitor door and folding keyboard

Enclosure for stand-alone siting, consisting of solid body, glazed door at the top, folding keyboard, component shelf, bottom door, rear door and welded base assembly. Enclosure body with mounting angles at the front and rear. System slots on a 25 mm pitch pattern, all round, for individual interior installation and two pairs of mounting angles for space-saving system configuration.

Glazed door, top:

With support frame latched from the inside, r/h hinge

- Vertical decorative trim panels
- Pane with screen-printed mask

Fold-out tray for keyboard:

- Enclosure with mouse support and cut-out in the rear panel, width 482.6 mm (19") x height 4 U
- Trim panel hinged at the bottom, with 2 retaining cords, with lock no. 3524
- Keyboard support with mousepad extension piece and 2 nylon tapes for keyboard
- With unlatching for glazed door, top

Bottom door:

- Vertical bars with locking rod and double-bit insert
- Hinged on right-hand side
- Door or installation plate folded

Rear door:

- with locking rod and double-bit insert, hinged on right-hand side
- Gland plates, three-part

Material:

Enclosure, door, gland plates, supports: Sheet steel

- Handles, decorative trim panels: Plastic
- Door trim panels: Aluminium

Surface finish:

- Zinc-plated gland plates

Colour:

- Enclosure, rear door: RAL 7035

Top glazed door:

- Vertical decorative trim panels: RAL 7035
- Pane with screen-printed mask: RAL 7015

Component shelf for monitor: RAL 7015

Folding support panel for keyboard:

- Enclosure: RAL 7035
- Front trim: RAL 7035/7015/9006

Bottom door:

- Vertical bars: RAL 7035
- Folded installation plate: RAL 7015

External dimensions WHD: 600 x 1600 x 600 mm

Model No.: 5366100

Manufacturer: Rittal GmbH & Co.KG