Rittal - The System.

Faster – better – everywhere.






CP 6535.010 Command panel housing with door

State: 08/12/2025 (Source: rittal.com/gr-en)



CP 6535.010 - Command panel housing with door Stainless steel

Command panel housing with door made from stainless steel 1.4301 (AISI 304), with handle strips made from plastic approved for use with foodstuffs. May be combined with support arm system CP40, stainless steel.







Features

Model No.	CP 6535.010
Design	With support arm connection CP 40, stainless steel
Material	Enclosure and door: Stainless steel 1.4301 (AISI 304) Handle strips: Plastic approved for use with foodstuffs, dyed blue
Surface finish	Brushed, grain 400
General colour	Stainless steel
Colour	Handle strips: similar to RAL 5002
Supply includes	Enclosure of all-round solid construction
	Cut-out and reinforcement for support arm system CP 40 stainless steel
	Fastener with guide plate
	Door with sealing frame and side handle strips
	Lock: 3 mm double-bit
Dimensions	Width: 300 mm
	Height: 300 mm
	Depth: 150 mm

© Rittal 2025 2

Features

IP protection category to IEC 60 529	IP 66
Protection category NEMA	NEMA 12
Note	The support arm connection and door hinge may be swapped over by rotating the enclosure 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C
Basic material	Stainless steel 1.4301 (AISI 304)
Note on Model No.	Matching mounting panel 5050.432 with dispatch bag 5050.507
Packs of	1 pc(s).
Net weight	5.985
Gross weight	6.3
Customs tariff number	94032080
EAN	4028177220362
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3