## Rittal - The System.

Faster – better – everywhere.





# TP 6704.600 **Pedestals**

State: 17/11/2025 (Source: rittal.com/gr-en)



#### TP 6704.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

#### **Features**

Model No.	TP 6704.600
Material	Enclosure: Sheet steel 1.5 mm
	Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in
	PU seal
	Mounting plate: Sheet steel
Surface finish	Enclosure, cover and door: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure open at top
	Door or double door with locking rod (with depth 400 mm at the
	front, with depth 500 mm at the front and rear)
	Mounting plate
	Gland plates
Dimensions mounting plate (W x H)	499 mm x 571 mm
Number of doors	1
Dimensions	Width: 600 mm
	Height: 675 mm
	Depth: 500 mm
IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Note	Mounting plate, depth-variable on a 25 mm pitch pattern
Packs of	1 pc(s).
Net weight	42.6

© Rittal 2025

### Features

Gross weight	45
Customs tariff number	94032080
EAN	4028177959880
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3