Rittal - The System.

Faster – better – everywhere.





CX 6722.000 CX console

State: 18/11/2025 (Source: rittal.com/gr-en)



CX 6722.000 - CX console

Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system.





Features

Model No.	CX 6722.000
Design	Console
Product description	Four widths create the ideal conditions for individual monitoring and three-piece assembly of the CX console system.
Material	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure Cover hinged at bottom, including cover retainer Open base for individual cable entry Lock: 3 mm double-bit
Dimensions	Width: 1,200 mm Height: 515 mm
Depth (top)	125 mm
Depth (bottom)	245 mm
IK Code	IK10
Note	A desk unit and pedestal are required for a 3-part console assembly.

© Rittal 2025

Features

IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 1
	NEMA 12
Basic material	Sheet steel
Dimensions	Width: 1,200 mm
	Height: 515 mm
	Depth (top): 125 mm
	Depth (bottom): 245 mm
Lock version	Cam
Lock insert	3 mm double-bit
Lock	Lock version: Cam
	Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	29
Gross weight	29.5
Customs tariff number	94032080
EAN	4028177983656
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3