

**Rittal – The System.**

Faster – better – everywhere.



**IW 6902.670**

**Enclosure attachment, tilting, top mounting**

State: 09/09/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IW 6902.670 - Enclosure attachment, tilting, top mounting

For mounting on IW worktops or other surfaces.



## Features

Model No.	IW 6902.670
Product description	With cable tube for protected cable entry.
Applications	For mounting on: IW worktop, prepared for enclosure attachment, surfaces, enclosure attachment/coupling CP-L rectangular 120 x 65 mm, attachment/housing coupling CP 40 (may also be used as tilting adaptor +100°/-60° for CP 40) To fit enclosures up to 20 kg with support arm connection: CP-40, CP-L rectangular 120 x 65 mm, CP-L Ø 130 mm, VESA Standard 75
Material	Sheet steel Concertina section: Plastic
Surface finish	Spray-finished
Colour	RAL 7024
Supply includes	Assembly parts
Tilt angle note	+100°/-60°, adjustable in 7.2° increments via clamping lever and may be limited to +100°/-15° using the stop screw supplied loose.
Tilt angle pitch pattern	7.2 °
OUT_TILT_ANGLE	-60 - 100 °
Packs of	1 pc(s).
Net weight	0.72
Gross weight	0.928

# Features

Customs tariff number	73182900
EAN	4028177325791
ECLASS 8.0	27189263

## Tender text

Enclosure attachment, tilting, top mounting

For mounting on:

- IW worktop, prepared for enclosure attachment
- CP-L, round
- Surfaces
- Enclosure attachment/coupling CP-L rectangular,
- Attachment/housing coupling CP-S (may also be used as tilting adaptor + 100°/-60° for CP-S)

To fit enclosures up to 20 kg with support arm connection

- CP-S
- CP-L rectangular
- CP-L round
- VESA Standard 75

With cable tube for protected cable entry.