

Rittal – The System.

Faster – better – everywhere.



DK 7044.150 Complete CAT 6 system

State: 19/08/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7044.150 - Complete CAT 6 system for Network Cable Organizer

The complete Network Cable Organizer system revolutionises structured cabling in all network racks from a depth of 800 mm. Surplus cable lengths – whether CAT 6 or fibre-optic – are simply withdrawn with a spring balancer.



Features

Model No.	DK 7044.150
Product description	Modern network infrastructures rely on maximum performance and the greatest possible flexibility in cabling. A useful component here is the Network Cable Organizer (NCO). The robust 1 U mounting frame is pre-configured with 24 cable cassettes and revolutionises conventional structured cabling with 8 times faster installation.
Benefits	<p>Minimise cable chaos – Prevent obstructions to the air circulation in the vicinity of network switches</p> <p>Always the right length: Surplus cable lengths – whether CAT 6 or fibre-optic – are simply withdrawn with a spring balancer</p> <p>Every cable is 100% tested and supplied with a corresponding measurement record</p> <p>Front access – Ideal for retrofitting into racks with a depth of 800 mm or more</p>
Technical specifications	<p>CAT 6 cable STP</p> <p>2 x RJ 45 connectors per cable</p> <p>Shielded RJ 45 connector with gold-coated pins</p> <p>Usable cable length per cassette: 1.6 m</p> <p>ISO/IEC 11801:2002, AWG 36, 100% copper, 250 MHz</p>
Applications	For use in all network racks from a depth of 800 mm.

Features

Function principle	Attachment to the front and rear 482.6 mm (19") level
Material	Mounting frame: Sheet steel Cassettes: Stainless steel, plastic (POM)
Colour	Mounting frame: RAL 9005 Cable: green
Supply includes	Complete CAT 6 system 24 CAT 6 cassettes Installation kit Assembly parts
Number cassettes max	24
Number cassettes preassembled	24
Dimensions	Width: 450 mm Height: 44 mm Depth: 600 mm
Operating temperature range	10 °C...45 °C
Ambient humidity (non-condensing)	95 %
Relative humidity (non-condensing)	10 %
Packs of	1 pc(s).
Customs tariff number	73269098
EAN	4028177917255
ECLASS 8.0	27189265