


Rittal – The System.

Faster – better – everywhere.



DK 7061.000

Telescopic slides

State: 06/02/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7061.000 - Telescopic slides for component shelves, for mounting on the VX enclosure frame and for upgrading existing VX and TS applications

For retrospectively converting fixed component shelves to full withdrawal by exchanging the fastening bolts or mounting rails (heavy-duty version) for the telescopic slides.

Features

| | |
|------------------------------------|---|
| Model No. | DK 7061.000 |
| Product description | Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Suitable for component shelf depth | 400 mm |
| Load capacity | 50 kg |
| Note | For installation and locking on a 25 mm pitch pattern in the enclosure depth. |
| Packs of | 2 pc(s). |
| Net weight | 1.37 |
| Gross weight | 1.569 |
| PCF per pack (cradle-to-gate) | 6 kg CO ₂ eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177123731 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

Telescopic slides for 400 mm deep component shelves

The telescopic slides are installed between the installation kit and a 400 mm deep component shelf.

The telescopic slides have a maximum load capacity of 50 kg and are lockable in two positions.

Material: sheet steel, zinc-plated

For component shelf depth: 400 mm