

Rittal – The System.

Faster – better – everywhere.



DK 7163.565 Cable support

State: 17/04/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7163.565 - Cable support hinged, with anti-kink device and clamp

Kink-free cable routing in the central part via mobile chain links, the attachment may be released on both sides, thanks to clamps.



Features

Model No.	DK 7163.565
Product description	For secure routing of connection cables from the component shelf to the clamping point. Kink-free cable routing in the central part via mobile chain links. The attachment may be released on both sides thanks to clamps.
Material	Sheet steel, zinc-plated Centre part: Plastic
Supply includes	Assembly parts
Note	Max. depth of component shelves = Enclosure depth - 200 mm.
To fit	Depth: > 600 mm
Packs of	1 pc(s).
Net weight	0.7 kg
Gross weight	0.78 kg
PCF per pack (cradle-to-gate)	2.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

Features

ETIM 9	EC000322
--------	----------

ECLASS 8.0	27400604
------------	----------

Product description	DK Cable support, kink-free, For D: > 600 mm, Max. depth component shelf = depth rack-200 mm
---------------------	--

Tender text

Kink-free cable support
for enclosures larger than 600 mm
Material: Sheet steel, zinc-plated, passivated