

Rittal – The System.

Faster – better – everywhere.



DK 7241.024 Patch panels

State: 13/04/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7241.024 - Patch panels for fibre-optic splicing box, depth-variable, and fibre-optic breakout box, 1 U

With cut-outs for population with fibre-optic couplings.

Features

Model No.	DK 7241.024
Product description	With cut-outs for population with fibre-optic couplings.
Applications	for fibre-optic splicing box, depth-variable, and fibre-optic breakout box, 1 U
Material	Sheet steel
Colour	RAL 7035
Number of locations	24
for fibre-optic coupling	E-2000 E-2000 duplex SC LC duplex
Note on Model No.	For E-2000 duplex only half of the locations are available.
Units	1 U
Packs of	1 pc(s).
Net weight	0.2 kg
Gross weight	0.263 kg
PCF per pack (cradle-to-gate)	1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC001129
ECLASS 8.0	19170113
Product description	DK Patch panel

Tender text

Patch panel, 1 U, for fibre-opt. splic. box
24-port E-2000/SC

For coupling: E-2000, E-2000 duplex (only half of the installation slots are available with E-2000 duplex versions) or SC. Number of installation slots:
24 x 1 U

Fixing measurement: 400 mm

Material: Sheet steel, spray finished in RAL 7035