


Rittal – The System.

Faster – better – everywhere.



DK 7320.794 Door comfort handle

State: 01/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

DK 7320.794 - Door comfort handle with door opener function

By actuating the lock mechanism, the door is released via the automatic door opening system.

Features

Model No.	DK 7320.794
Product description	By actuating the lock mechanism, the door is released via the automatic door opening system. Prepared for the installation of standard commercially available profile half-cylinders, 40 mm, SZ lock and push-button inserts. Length: 302 mm
Colour	RAL 7035
Supply includes	Connection cable (3 m)
Length of connection cable	3 m
With DC	3 A
Operating temperature range	5 °C...40 °C
Packs of	1 pc(s).
Net weight	0.81
Gross weight	0.831
Customs tariff number	83015000
EAN	4028177636019
ETIM 9	EC001770
ECLASS 8.0	27390190

Tender text

7320.794

Door comfort handle

The handle for TS IT racks is designed with an integrated switching contact as the opener. The system can be used in combination with the CMC III Door Control Module. Triggering of the switch contact is detected by the CMC III Door Control Module, and the solenoids are de-energised so that the door of a rack can be released and/or opened. Prepared for the installation of commercially available semi-cylinders, 40 mm, as well as SZ lock and push-button inserts.

Technical specifications:

Temperature application range:

5 °C to 40 °C

Humidity range:

5% to 95% relative humidity, non-condensing

Rated voltage: 24 V DC

Rated current: max. 3 A

Length: 302 mm.

Colour: RAL 7035