

Rittal – The System.

Faster – better – everywhere.



TE 7526.750 Module plates

State: 04/03/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7526.750 - Module plates for TE

The base area of the TE may be varied as required using the module plates.

Features

Model No.	TE 7526.750
Design	Compensating panel
Product description	The base area of the TE may be varied as required using the module plates.
Applications	Please note when selecting suitable gland plates: Enclosure width minus 150 mm Enclosure depth minus 50 mm
Material	Sheet steel, zinc-plated
Supply includes	Assembly parts
Dimensions	Width: 450 mm Depth: 50 mm
To fit	Enclosure type: TE Width: 600 mm
Packs of	1 pc(s).
Net weight	0.321 kg
Gross weight	0.363 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	TE Module plate, WxD: 450x50 mm, Compensating panel, For W: 600 mm

Tender text

Module plate, solid

Solid module plate

450 mm wide module plate, 50 mm deep module plate

Material: Sheet steel, zinc-plated