


Rittal – The System.

Faster – better – everywhere.



DK 7827.050 Cable route

State: 01/07/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.050 - Cable route for TS 8

For cable routing between two 482.6 mm (19") mounting angles in bayed enclosure suites (enclosure width 800 mm, mounting angles fitted centrally), suitable for L-shaped and cranked mounting angles.

Features

Model No.	DK 7827.050
Product description	For cable routing between two 482.6 mm (19") mounting angles in bayed enclosure suites (enclosure width 800 mm, mounting angles fitted centrally). Suitable for L-shaped and cranked mounting angles.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Assembly parts
To fit	Enclosure type: TS 8 Width: 800 mm
Packs of	1 pc(s).
Net weight	1.2
Gross weight	1.22
Customs tariff number	73269098
EAN	4028177345515
ECLASS 8.0	27400604

Tender text

Cable route, RAL 7035

For routing cables between 2 x 19" mounting angles in DK-TS enclosures. Suitable for use with L-shaped as well as cranked mounting angles.

Material: Sheet steel, spray finished in RAL 7035