

Rittal – The System.

Faster – better – everywhere.



SK 7980.100 Fan expansion kit

State: 10/07/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 7980.100 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

Features

Model No.	SK 7980.100
Product description	For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate.
Supply includes	Fan Connection cable (0.61 m) Assembly parts
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 108 m ³ /h At 60 Hz: 120 m ³ /h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 14 W At 60 Hz: 12 W
Dimensions	Width: 119 mm Height: 119 mm Depth: 25 mm
Operating temperature range	-20 °C...70 °C
Noise level	At 50 Hz: 34 dB(A) At 60 Hz: 34 dB(A)
Packs of	1 pc(s).
Net weight	0.43 kg
Gross weight	0.486 kg
Customs tariff number	84145915
ETIM 9	EC000320
ECLASS 8.0	27180716
Product description	DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD: 119x119x25 mm, 230 V, 1 ~, 50/60 Hz

Tender text

EL fan expansion kit

Rated operating voltage: 230V;

Power consumption: 14/12

W at 50/60 Hz;

Air throughput (unimpeded air flow): 108/120 m³/h at
50/60 Hz;

Temperature range: -20°C to +70°C

Dimensions (W x H x D): 119 mm x 119 mm x 25 mm