### Rittal - The System.

Faster – better – everywhere.





TS 8188.235

# Side panel, screw-fastened, sheet steel

State: 29/10/2025 (Source: rittal.com/gr-en)



## TS 8188.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

#### **Features**

Model No.	TS 8188.235
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface
Material	Sheet steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 7035
Supply includes	Assembly parts
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure  Area available for population: External dimension – 100 mm
To fit	Enclosure type: TS TS IT Height: 1,800 mm Depth: 800 mm
IP protection category to IEC 60 529	IP 55
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	34
Gross weight	35.2
Customs tariff number	94039910
EAN	4028177243712

© Rittal 2025

#### **Features**

ETIM 9	EC002524
ECLASS 8.0	27182101

#### Tender text

Side panels, screw-fastened, for DK TS
Easy positioning on the frame with the location aid.
The enclosure panel holders with earthing insert ensure automatic potential equalisation and higher EMC protection.

They may optionally be fitted from the inside or outside of the enclosure. When using TS side panel hinges an opening angle of 180° is possible.

Material: 1.5 mm sheet steel

Protection category: IP 55

Surface finish: Dipcoat-primed, powder-coated in

textured RAL 7035

For enclosure dimensions: H: 1800 mm D: 800 mm Side panels, screw-fastened DK 8188.235 Hinge for side panels (option), screw-fastened DK 8800.010

© Rittal 2025 3