

**Rittal – The System.**

Faster – better – everywhere.



**TS 8612.040**

**TS punched section with mounting  
flange, 17 x 73 mm**

State: 05/04/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.040 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



## Features

|                      |  |
|----------------------|--|
| Model No.            | TS 8612.040  |
| Design               | For the inner mounting level and for mounting on doors   |
| Product description  | For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.  |
| Material             | Sheet steel  |
| Surface finish       | Zinc-plated  |
| Supply includes      | Assembly screws  |
| Length               | 390 mm   |
| To fit door width    | 500 mm   |
| Installation options | On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round<br>On the horizontal VX SE enclosure section, top in the depth<br>In TP via rail for interior installation: In the width, for inner mounting level<br>As a mounting kit for component shelves in TS, VX SE, simply locate and secure |
| Assembly instruction | The rail for internal mounting is required when installing in TP   |

# Features

|                               |   |
|-------------------------------|---|
| To fit                        | Enclosure type: VX SE<br>TP<br>PC<br>IW<br>Width/depth: 400 mm  |
| Packs of                      | 4 pc(s).  |
| Net weight                    | 1.6 kg  |
| Gross weight                  | 1.75 kg   |
| PCF per pack (cradle-to-gate) | 6.7 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                    |
| Customs tariff number         | 73269098  |
| ETIM 9                        | EC002625  |
| ECLASS 8.0                    | 27189234  |
| Product description           | TS punched section with mounting flange, 17 x 73 mm, for inner mounting level: for W/D: 400 mm, for door width: 500 mm, L: 390 mm |