

Rittal – The System.

Faster – better – everywhere.



VX 8617.190

Punched section with mounting flange, 23 x 64 mm

State: 28/06/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.190 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



Features

Model No.	VX 8617.190
Product description	For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.
Benefits	Simply locate into the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure height 1800 mm, on the inner mounting level
VX SE installation options	In enclosure width/height 1800 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
VX base/plinth installation options	In base/plinth width 1800 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket

Features

To fit	Enclosure type: VX VX IT VX SE Suitable for width or height or depth: 1,800 mm
To fit	Base/plinth system VX
Packs of	4 pc(s).
Net weight	7.2 kg
Gross weight	7.72 kg
PCF per pack (cradle-to-gate)	40.25
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level

Approvals

Explanations	PCF-declaration
--------------	-----------------