



VX 8617.500 - Baying bracket, internal for VX, VX IT

Supports flexible positioning and all-round mounting at the baying point. Fast, secure installation, optionally from the front or from the side, may also be used for baying to the VX base/plinth system.

Features

Model No.	VX 8617.500
Benefits	Fast, secure installation either from the front or from the side For all-round installation on the baying joint May be flexibly positioned to avoid collisions with installed equipment
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Baying bracket, internal Baying seal Assembly parts
Note	1 pack is sufficient for one baying joint
To fit	Enclosure type: VX VX IT
IP protection category to IEC 60 529	IP 55
Packs of	6 pc(s).
Net weight	1.38
Gross weight	1.44
Customs tariff number	83024900
EAN	4028177919327
E-Number Sweden	E3465117
ETIM 9	EC002622
ECLASS 8.0	27189263

Approvals

Approvals

UL + C-UL - FTTA