


# Rittal – The System.

Faster – better – everywhere.



## VX 8617.501

### Baying block, internal

State: 08/12/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.501 - Baying block, internal for VX, VX IT

Supports flexible positioning and all-round mounting at the baying point. Side mounting creates a flush surface, suitable for top mounting.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | VX 8617.501  |
| Benefits                            | Side mounting creates a flush surface to the extrusion, suitable for top mounting, thus avoiding collisions with installed equipment<br>For all-round installation on the baying joint |
| Material                            | Die-cast zinc  |
| Supply includes                     | Baying block, internal<br>Baying seal<br>Assembly parts  |
| Note                                | For baying enclosures with a width/depth > 800 mm, 2 packs are required for installation   |
| To fit                              | Enclosure type: VX<br>VX IT  |
| Type rating to UL 50E               | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12  |
| IP protection category to IEC 60529 | IP 55  |
| Packs of                            | 6 pc(s).   |
| Net weight                          | 0.822  |
| Gross weight                        | 0.86   |
| Customs tariff number               | 76169990   |
| EAN                                 | 4028177919334  |
| E-Number Sweden                     | E3465118   |
| ETIM 9                              | EC002622   |

# Features

---

|            |          |
|------------|----------|
| ECLASS 8.0 | 27189263 |
|------------|----------|

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|