Rittal - The System.

Faster - better - everywhere.





VX 8618.000 Glazed door

State: 31/10/2025 (Source: rittal.com/gr-en)



VX 8618.000 - Glazed door for VX

Instead of a sheet steel door or rear panel.

Features

Model No.	VX 8618.000
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035
	Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door
	Locking rod with double-bit insert
	180° hinges (4)
IK Code	IK08
Note	Lock components for frame 8618.110 are required when mounting
	instead of the rear panel
Type rating to UL 50E	Type 1
	Type 12
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: VX
	Width: = 600 mm
	Height: = 1,800 mm
Packs of	1 pc(s).
Net weight	12.4
Gross weight	13
EAN	4028177921085
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025

Approvals

Approvals	UL + C-UL - FTTA
Certificates	Protection category

© Rittal 2025 3