


Rittal – The System.

Faster – better – everywhere.



VX 8618.040 Glazed door

State: 08/07/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8618.040 - Glazed door for VX

Instead of a sheet steel door or rear panel.

Features

| | |
|-------------------------------------|---|
| Model No. | VX 8618.040 |
| Product description | Instead of a sheet steel door or rear panel. |
| Material | Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005 |
| Supply includes | Glazed door Locking rod with double-bit insert 180° hinges (4) |
| IK Code | IK08 |
| Note | Lock components for frame 8618.110 are required when mounting instead of the rear panel |
| Type rating to UL 50E | Type 1 Type 12 |
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: VX Width: = 600 mm Height: = 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 14.6 kg |
| Gross weight | 15.4 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |

Features

| | |
|---------------------|-------------------------------------|
| Product description | VX Glazed door, for WH: 600x2200 mm |
|---------------------|-------------------------------------|

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|

| | |
|--------------|---------------------|
| Certificates | Protection category |
|--------------|---------------------|