

# Rittal – The System.

Faster – better – everywhere.



## VX 8660.090

## Base/plinth trim panels, vented

State: 01/07/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8660.090 - Base/plinth trim panels, vented for base/plinth system VX, sheet steel

For venting the enclosure via the base/plinth. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Thanks to the optional trim panel attachment, the vented trim panels may also be fitted at the side of the base/plinth corner piece.

## Features

Model No.	VX 8660.090
Design	Vented
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 100 mm
To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width/depth: 600 mm
Type rating to UL 50E	Type 1 Type 12
Weight/pack	1.42 kg
Packs of	2 pc(s).
To fit	for base/plinth system VX, sheet steel
Net weight	1 kg
Gross weight	1.319 kg

# Features

---

PCF per pack (cradle-to-gate)	17.01
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base/plinth trim panel, vented, for W/D: 600 mm, sheet steel

---

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------