

# Rittal – The System.

Faster – better – everywhere.



## VX 8700.050

## Side panels, screw-fastened, stainless steel

State: 28/06/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8700.050 - Side panels, screw-fastened, stainless steel for VX

Side panels, screw-fastened, stainless steel, for VX.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | VX 8700.050   |
| Benefits                            | Time-saving assembly thanks to clip-in side panel holder<br>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside<br>Easy positioning in the height and depth with the location aid<br>One-person assembly<br>Earthing bolts with large, paint-free contact surface for optimum contact |
| Material                            | Stainless steel 1.4301 (AISI 304), 1.5 mm   |
| Surface finish                      | Brushed, grain 400  |
| Supply includes                     | Assembly parts  |
| To fit                              | Enclosure type: VX<br>Height: = 2,000 mm<br>Depth: = 600 mm   |
| IP protection category to IEC 60529 | IP 55<br>IP 66  |
| Type rating to UL 50E               | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12   |
| Basic material                      | Stainless steel   |
| Packs of                            | 2 pc(s).  |
| Net weight                          | 27.8 kg   |
| Gross weight                        | 28.8 kg   |

# Features

---

|                       |   |
|-----------------------|---|
| Customs tariff number | 94039910  |
| ETIM 9                | EC002524  |
| ECLASS 8.0            | 27182101  |
| Product description   | VX Side panel, screw-fastened, for HD: 2000x600 mm, stainless steel, 1.4301 |

---

# Approvals

---

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|