


Rittal – The System.

Faster – better – everywhere.



DK 9055.310 Monitor/keyboard unit

State: 25/07/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 9055.310 - Monitor/keyboard unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



Features

Model No.	DK 9055.310
Benefits	Analog and digital video input Cables are safely routed in the energy chain Lockable at the front Simple, one-man installation.
Colour	RAL 7035
Supply includes	Monitor/keyboard unit, 1 U VGA cable DVI cable USB cable Earthing-pin mains cable with 17" TFT display and VGA/DVI connection 2 PS/2 cables Keyboard with integral touchpad
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Max. power consumption with closed monitor unit	1 W
Max. power consumption in operation	32 W

Features

Interfaces	VGA (D-Sub HD 15-pole) DVI 1 x USB PS/2
Connector (type)	IEC 320 connector C14
Layout	German
Dimensions	Width: 482.6 mm Depth: 680 mm
Operating temperature range	5 °C...45 °C
Installation dimensions	Installation depth (min.): 680 mm Installation depth (max.): 850 mm
Display features	Diagonal: 432 mm (17") Format: 4 : 3 Contrast ratio: Contrast ratio approx. 1000:1 Display brightness: 350 cd/m ² Resolution of display: 1280 x 1024 pixels Number of colours: 16,700,000
Packs of	1 pc(s).
Net weight	15.5
Gross weight	16.5
Customs tariff number	85286200
EAN	4028177638372
ETIM 9	EC001428
ECLASS 8.0	19200201

Approvals

Explanations	Declaration of conformity
--------------	---------------------------