#### Rittal – The System.

Faster – better – everywhere.





# SV 9340.030 Busbar support

State: 30/10/2025 (Source: rittal.com/gr-en)



## SV 9340.030 - Busbar support 1-pole

#### **Features**

Model No.	SV 9340.030
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
To fit busbars	12 x 5/10 15 x 5 - 30 x 10
To fit busbars	Flat copper busbars
Number of poles	Single-pole
Note	Multi-pole systems with 60 mm bar centre distance may be configured by baying the busbar supports Support suitable for AC and DC applications.
Note on Model No.	If 12 x 5/10 mm busbars are used, spacer 9340.090 is additionally required
Rated operating voltage	1000 V, 1~ 1500 V (DC)
PEN/N/PE support	Yes
Packs of	4 pc(s).
Net weight	0.2
Gross weight	0.24
Customs tariff number	85369010
EAN	4028177583580
ETIM 9	EC001166
ECLASS 8.0	27400607

© Rittal 2025

### Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3