

Rittal – The System.

Faster – better – everywhere.



SV 9340.300 OM supports

State: 04/07/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SV 9340.300 - OM supports without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.300
Design	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	without support frame, 2 x TS 45D
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0.153 kg
Gross weight	0.202 kg
Customs tariff number	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV OM Support, WH: 45x208 mm, support rails 2xTS 45D, without contact system

Approvals

Approvals

ABS
DNV
Lloyds Register
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK