

Rittal – The System.

Faster – better – everywhere.



SV 9340.870 Cable set

State: 14/05/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.870 - Cable set for OM adaptors with spring terminal block

Pre-assembled connection cables for individual connection of switchgear.



Features

Model No.	SV 9340.870
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 10 = 5.26 mm ² \approx 6 mm ²
Note	AWG = American Wire Gauge
Dimensions	Length: 140 mm
Packs of	15 pc(s).
Net weight	0.12 kg
Gross weight	0.13 kg
Copper weight (kg per piece)	0.006
Customs tariff number	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302
Product description	SV Cable set, AWG 10, L: 140 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK