

**Rittal – The System.**

Faster – better – everywhere.



# SV 9344.610 Box terminal

State: 15/05/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.610 - Box terminal for NH fuse-switch disconnectors

For NH fuse-switch disconnectors size 1 to 3 with screw terminal. For direct connection of round and sector-shaped conductors.



## Features

|   |   |
|---|---|
| Model No.                               | SV 9344.610   |
| Product description                     | For direct connection of round and sector-shaped conductors and laminated copper bars. Suitable for NH fuse-switch disconnectors with screw terminal. |
| Material                                | Cast brass  |
| Surface finish                          | Nickel-plated   |
| Clamping area for laminated copper bars | Clamping area width: 20 mm<br>Clamping area height: 14 mm   |
| Type of electrical connection           | Box terminal  |
| For size                                | 1   |
| OUT_COL_CROSS_SECTION_SEC TOR_CONDUCTOR | 50 - 150 mm <sup>2</sup>  |
| Connection of round conductors          | 35 - 150 mm <sup>2</sup>  |
| Round conductor cross-section           | 35 - 150 mm <sup>2</sup>  |
| Packs of                                | 3 pc(s).  |
| Net weight                              | 0.171 kg  |
| Gross weight                            | 0.175 kg  |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 73182900   |
| ETIM 9                | EC001894   |
| ECLASS 8.0            | 27400609   |
| Product description   | SV Box terminal, for NH fuse-switch disconnecter, size 1 (with screw terminal), round conductor connection 35-150 mm <sup>2</sup> , clamping area WH: 20x14 mm |