

Rittal – The System.

Faster – better – everywhere.



SV 9630.000

Mini-PLS bus-mounting fuse bases

State: 02/05/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9630.000 - Mini-PLS bus-mounting fuse bases

Rated current 63 A



Features

| | |
|--------------------------------|--|
| Model No. | SV 9630.000 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 9011 Cover: RAL 7035 |
| Note | Wire end ferrules should be used with fine wire conductors |
| Type of electrical connection | Box terminal |
| Fuse inserts | D 02-E 18 (adaptor sleeve) |
| Rated operating voltage | 400 V |
| Rated current max. | 63 A |
| Dimensions | Width: 38 mm Height: 160 mm |
| Connection of round conductors | 1.5 - 16 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.3 kg |
| Gross weight | 0.316 kg |
| Copper weight (kg per piece) | 0.11 |

Features

| | |
|-----------------------|---|
| Customs tariff number | 85369095 |
| ETIM 9 | EC001644 |
| ECLASS 8.0 | 27142120 |
| Product description | SV Mini-PLS bus-mounting fuse base, D02-E18, 63 A, 400 V, 3-pole, round conductor connection 1,5-16 mm ² , adaptor sleeve, including cover plate |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|