### Rittal – The System.

Faster - better - everywhere.





# SV 9676.730 Direct connection terminal

State: 04/11/2025 (Source: rittal.com/gr-en)



# SV 9676.730 - Direct connection terminal for round conductors

For the direct connection of round conductors 95 – 300 mm<sup>2</sup> (single-wire and multi-wire).

#### **Features**

Model No.	SV 9676.730
Product description	For connecting round conductors to a busbar distributor system made from flat copper. Suitable for 10 mm bar thickness.
Material	Connection clamp: Brass, tin-plated Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Assembly instruction	The required screw length must be selected in line with the busbar width W, i.e. length = W + fastening measurement. Screws are not included with the supply.  Busbar claw with threaded insert M10
Number of bars per conductor	2
Connection of round conductors	95 - 300 mm²
Mounting dimensions	60 mm
Packs of	1 pc(s).
Net weight	0.32
Gross weight	0.327
Customs tariff number	85369010
EAN	4028177625549
ETIM 9	EC002270
ECLASS 8.0	27400613

© Rittal 2025

## **Approvals**

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025 3