

Rittal – The System.

Faster – better – everywhere.



SV 9677.952

Current transformer

State: 31/07/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.952 - Current transformer

For inductive measurement of current flow.

Features

Model No.	SV 9677.952
Product description	Compact design without altering the installation depth via mechanical integration into the top-mounting components (185 mm centre-to-centre spacing); this allows space-saving assembly.
Material	Polyamide
For size	3
To fit Model No.	9677.360 9677.365 9677.380 9677.930
Rated power input	1.5 VA
Type of electrical connection	Box terminal
Insulation material (class)	H
Primary current	500 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm ²
Rated frequency	50 - 60 Hz
Packs of	1 pc(s).
Net weight	0.136
Gross weight	0.146

Features

Customs tariff number	85043129
EAN	4028177984431
ETIM 9	EC002048
ECLASS 8.0	27141146