

Rittal – The System.

Faster – better – everywhere.



CS 9783.520

Outdoor Basic enclosures

State: 04/04/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9783.520 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



Features

Model No.	CS 9783.520
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.
Material	Aluminium AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 400 mm

Features

Dimensions	Overall height: 1,355 mm Rain canopy width: 850 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 712 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height base/plinth: 100 mm
------------	---

Type rating to UL 50E	Type 3R
-----------------------	---------

IP protection category to IEC 60529	IP 55
-------------------------------------	-------

IK Code	IK10
---------	------

Basic material	Aluminium
----------------	-----------

Packs of	1 pc(s).
----------	----------

Net weight	46 kg
------------	-------

Gross weight	48 kg
--------------	-------

Customs tariff number	94032080
-----------------------	----------

ETIM 9	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------
