

# Rittal – The System.

Faster – better – everywhere.



## CS 9783.550

## Outdoor Basic enclosures

State: 08/11/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9783.550 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



## Features

|                     |   |
|---------------------|---|
| Model No.           | CS 9783.550   |
| Product description | Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.   |
| Material            | Aluminium AlMg3   |
| Surface finish      | Powder-coated<br>UV-resistant pure polyester  |
| Colour              | RAL 7035  |
| Supply includes     | Single-walled outdoor enclosure, fully preconfigured<br>Basic enclosure with gland plate, three-part<br>25 mm system punchings in the roof, base, front and in the enclosure depth<br>Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027<br>Transport plinth with screw-fastened trim panels front and rear<br>Rain canopy |
| Dimensions          | Width: 600 mm<br>Height: 1,200 mm<br>Depth: 400 mm  |

# Features

---

|            |   |
|------------|---|
| Dimensions | Overall height: 1,355 mm<br>Rain canopy width: 650 mm<br>Rain canopy height: 55 mm<br>Rain canopy depth: 450 mm<br>Clearance width: 512 mm<br>Clearance height: 1,112 mm<br>Clearance depth: 349 mm<br>Height base/plinth: 100 mm |
|------------|---|

---

|                       |         |
|-----------------------|---------|
| Type rating to UL 50E | Type 3R |
|-----------------------|---------|

---

|                                     |       |
|-------------------------------------|-------|
| IP protection category to IEC 60529 | IP 55 |
|-------------------------------------|-------|

---

|         |      |
|---------|------|
| IK Code | IK10 |
|---------|------|

---

|                |           |
|----------------|-----------|
| Basic material | Aluminium |
|----------------|-----------|

---

|          |          |
|----------|----------|
| Packs of | 1 pc(s). |
|----------|----------|

---

|            |       |
|------------|-------|
| Net weight | 38.95 |
|------------|-------|

---

|              |    |
|--------------|----|
| Gross weight | 41 |
|--------------|----|

---

|     |               |
|-----|---------------|
| EAN | 4028177569157 |
|-----|---------------|

---

|        |          |
|--------|----------|
| ETIM 9 | EC000261 |
|--------|----------|

---

|            |          |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|

---