Rittal – The System.

Faster – better – everywhere.





KL 1530.010 Terminal boxes KL

State: 13.11.2025. (Source: rittal.com/hr-hr)



KL 1530.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

Features

Model No.	KL 1530.010	
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea	
Surface finish	Enclosure and cover: Brushed, grain 180	
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes	
Protection category NEMA	NEMA 4X	
Protection category to IEC 60 529	IP 66	
IK Code	IK08	
Dimensions	Width: 400 mm Height: 300 mm Depth: 120 mm	
Material thickness - cover	1,25 mm	
Material thickness - enclosure	1,25 mm	
Lock	Number of locks: 4	
Basic material	Stainless steel 1.4301 (AISI 304)	
Packs of	1 pc(s).	
Net weight	4.5	
Gross weight	4.6	
Customs tariff number	84879090	
EAN	4028177663350	
E-Number Sweden	E3404381	
ETIM 9	EC000261	
ETIM 8	EC000261	

© Rittal 2025

Features

ECLASS 8.0	S 8.0 27180101

Approvals

Approvals	Bureau Veritas DNV-GL UL + C-UL (listed)	
Explanations	Declaration of conformity Declaration of conformity UK	

© Rittal 2025 3