

Rittal – The System.

Faster – better – everywhere.



EL 2094.300 Captive nuts

State: 05.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



EL 2094.300 - Captive nuts

Captive nut, with M6 thread, with contact

Features

Model No.	EL 2094.300
Design	with contact
Product description	For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure.
Dimensions	Thread: M6
For material thicknesses	1.2 - 1.5 mm
Packs of	50 pc(s).
Net weight	0,15 kg
Gross weight	0,23 kg
Customs tariff number	73181692
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815
Product description	EL Captive nuts, M6, With contact, For metal thickness: 1,2-1,5 mm