

# Rittal – The System.

Faster – better – everywhere.



## SG 2370.171

## LED steady light component

State: 10.07.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2370.171 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SG 2370.171   |
| Design                            | LED steady light component  |
| Benefits                          | With 360° signal transmission thanks to optimised prism system<br>Configuration of up to five components with the same voltage. |
| Function principle                | A modular layout is possible with connection, optical and acoustic components and a label panel                                 |
| Material                          | Enclosure of polyamide<br>Cap: Transparent polycarbonate  |
| Colour                            | Yellow  |
| Protection category to IEC 60 529 | IP 65 if a cover or acoustic component is fitted at the top   |
| Rated operating voltage           | 230 V   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0,072 kg  |
| Gross weight                      | 0,073 kg  |
| Customs tariff number             | 85311095  |
| ETIM 9                            | EC000232  |
| ETIM 8                            | EC000232  |
| ECLASS 8.0                        | 27371220  |
| Product description               | SG LED steady light component, yellow   |

## Approvals

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---