



# SG 2372.130

## Signal pillar LED compact

State: 07.05.2026. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2372.130 - Signal pillar LED compact

Extremely long service life of the LEDs, minimal assembly work and low warehousing costs.

## Features

Model No.	SG 2372.130
Design	1-stage, red
Product description	Transmission angle: 3 x 120°, supplied state: Steady light. Flashing function controllable via PLC
Benefits	Complete, ready-to-connect solution Minimal build height Long LED service life Minimal assembly work and warehousing costs
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Diameter	72 mm
Type of electrical connection	Screw terminals
Light	LEDs
Rated insulation voltage	< 60 V DC
Dimensions	Height: 107 mm
Operating temperature range	-20 °C...70 °C
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V 24 V (DC)
Packs of	1 pc(s).
Net weight	0,219 kg
Gross weight	0,233 kg
Customs tariff number	85311095
ECLASS 8.0	27371230

# Features

---

Product description	SG Signal pillar, LED-compact, 24 V AC/DC, 1-stage, red
---------------------	---

# Approvals

---

Approvals	UR
-----------	----

---

Explanations	Declaration of conformity
	Declaration of conformity UK