

Rittal – The System.

Faster – better – everywhere.



SG 2374.060

Incandescent lamps

State: 24.06.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2374.060 - Incandescent lamps for steady light components

With BA 15d base.

Features

| | |
|---|---|
| Model No. | SG 2374.060 |
| Product description | With BA 15d base. |
| Benefits | Simple assembly and contact via bayonet fastener. |
| Function principle | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel |
| Power consumption (approx.) | 5 W |
| Rated impulse withstand voltage, phase to phase | 28 V AC |
| Rated insulation voltage | 2000 V AC |
| Rated operating voltage | 24 V |
| Packs of | 3 pc(s). |
| Net weight | 0.024 |
| Gross weight | 0.026 |
| Customs tariff number | 85392198 |
| EAN | 4028177219885 |
| ETIM 9 | EC000232 |
| ETIM 8 | EC000232 |
| ECLASS 8.0 | 27371220 |