

Rittal – The System.

Faster – better – everywhere.



SZ 2412.325 Earthing braid

State: 23.08.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2412.325 - Earthing braid

Tin-plated copper, in various lengths and cross sections with press-fitted contact rings, earthing straps counteract the current displacement effect at high frequencies, flexible connection opportunities.



Features

| | |
|-----------------------|--|
| Model No. | SZ 2412.325 |
| Product description | Tin-plated copper, in various lengths and cross-sections with press-fitted contact rings. Earthing braids counteract the current displacement effect at high frequencies, whilst at the same time offering highly flexible connection opportunities. |
| Cross-section | 25 mm ² |
| Connection | M8 – M8 |
| Note | Please observe the assembly instructions or PE conductor brochure for the relevant enclosure or case system. |
| Dimensions | Length: 300 mm |
| Packs of | 10 pc(s). |
| Net weight | 0.75 |
| Gross weight | 0.788 |
| Customs tariff number | 74198010 |
| EAN | 4028177022607 |
| ETIM 9 | EC000839 |
| ETIM 8 | EC000839 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27062302 |
|------------|----------|

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|