


# Rittal – The System.

Faster – better – everywhere.



## SZ 2422.000

## Spacer

State: 01.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2422.000 - Spacer for roof plate

To raise the roof for ventilation purposes, in three different heights. Not suitable for crane transportation.



## Features

|                               |  |
|-------------------------------|--|
| Model No.                     | SZ 2422.000  |
| Product description           | To raise the roof for ventilation purposes, in three different heights.  |
| Material                      | Hexagon steel section  |
| Surface finish                | Zinc-plated  |
| Supply includes               | Assembly parts   |
| Assembly instruction          | Not suitable for crane transportation  |
| Dimensions                    | Height: 10 mm  |
| Dimensions                    | Thread: M12  |
| To fit                        | Enclosure type: VX<br>TS   |
| Packs of                      | 4 pc(s).   |
| Net weight                    | 0.12   |
| Gross weight                  | 0.161  |
| PCF per pack (cradle-to-gate) | 0.6 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73269098   |

# Features

|                 |               |
|-----------------|---------------|
| EAN             | 4028177022775 |
| E-Number Sweden | E7239751      |
| ETIM 9          | EC002625      |
| ETIM 8          | EC002625      |
| ECLASS 8.0      | 27189234      |