

# Rittal – The System.

Faster – better – everywhere.



## SZ 2561.300 Plastic gland plate

State: 11.07.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2561.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

Model No.	SZ 2561.300
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.
Material	Plastic to UL 94-V0
Colour	Similar to RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 256 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 1
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12
No. of cable entries and Ø (mm) min.-max.	15 x 5-11 22 x 10-15 8 x 15-25 4 x 19-34 1 x 26-54
Packs of	1 pc(s).
Net weight	0,36 kg
Gross weight	0,365 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211

# Features

---

ECLASS 8.0

27142421

---

Product description

SZ Plastic gland plates, for AX, with membranes, WD: 256x149 mm,  
for gland plates size 1

# Approvals

---

Approvals

UL + C-UL - FTTA