


Rittal – The System.

Faster – better – everywhere.



SZ 2561.500

Plastic cable gland plates

State: 30.01.2026. (Source: rittal.com/hr-hr)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2561.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

Features

| | |
|--|---|
| Model No. | SZ 2561.500 |
| Product description | Simply pierce the plastic with a sharp object, and pull through the cable. |
| Material | Plastic to UL 94-V0 Halogen free |
| Colour | Similar to RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions | Width: 330 mm Depth: 90 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 3 |
| Protection category to IEC 60 529 | IP 65 |
| No. of cable entries and Ø (mm) min.-max. | 17 x 6-11 27 x 10-15 2 x 15-21 4 x 16-25 2 x 19-34 |
| Packs of | 1 pc(s). |
| Net weight | 0.365 |
| Gross weight | 0.37 |
| Customs tariff number | 39269097 |
| EAN | 4028177325593 |
| E-Number Sweden | E3404727 |

Features

ETIM 9 EC000211

ETIM 8 EC000211

ECLASS 8.0 27142421